

Part Number Index

Sorted by Prefix

034

034-289K A-92

043

043-345 G-38

125

125-3481 C-38

134

134-034 A-91

134-061 A-93

134-084 C-41

134-117 A-91

134-1083 A-32

134-1084 A-32

134-1085 A-32

134-1086 A-32

134-1450 G-14

134-1451 G-14

134-1460 G-14

134-1504 A-74

134-1510 A-74

134-1511 A-74

134-1700 A-28

134-1710 A-28

141

141-098 A-79

141-337 A-91

141-338 A-91

141-351 A-91

141-426 H-18

141-464 H-14

141-570 A-77, A-93

141-0518 G-12

141-0520 A-30

141-0521 A-30

141-0522 A-72

141-0530 A-72

141-0566 G-8

141-0573 A-77

141-0574 G-12

141-0575 G-12

141-0590 C-28

141-0591 C-28

141-0592 C-28

141-0593 C-28

141-0600 G-6

141-0601 H-14

142

142-0229 C-32

142-0238 C-32

142-0239 C-32

142-0240 C-32

142-0241 C-32

142-0242 C-32

142-0243 C-32

142-0244 C-32

142-0245 C-32

142-0246 C-32

142-0247 C-32

142-0258 C-32

142-0259 C-32

142-0260 C-32

142-0261 C-32

142-0262 C-32

142-0263 C-32

142-0264 C-32

142-0265 C-32

142-0266 C-28

142-0267 C-32

142-0272 C-32

142-0274 H-8

142-0277 H-8

142-0279 H-8

142-0283 C-32

142-0284 C-32

142-0285 C-32

142-0286 C-32

142-0287 C-32

142-0288 C-32

142-0289 C-32

142-0290 C-32

142-0291 C-32

142-0292 C-32

142-0293 C-32

142-0295 C-32

142-0311 H-8

142-0312 H-8

142-0313 H-8

142-0316 C-32

142-0327 C-32

142-0331 H-8

142-0332 C-32

142-0333 C-32

142-0344 A-78, H-8

142-0345 C-32

142-0346 C-32

142-0352 C-32

142-0354 C-32

142-0355 C-32

142-0356 C-32

142-0359 C-32

142-0371 H-8

142-0373 A-78, A-92, C-40, H-8

142-0379 C-32

142-0382 C-32

142-0383 C-32

142-0384 C-32

142-0394 C-32

142-0395 C-32

142-0396 C-32

142-0397 C-32

142-0398 C-32

142-0399 C-32

142-0401 C-32

142-0402 C-32

142-0410 C-32

142-0411 C-32

142-0412 C-32

142-0413 C-32

142-0414 C-32

142-0415 C-32

142-0416 C-32

Part Number Index

142 (Continued)

142-0417	C-32
142-0418	C-32
142-0419	C-32
142-0420	C-32
142-0421	C-32
142-0422	C-32
142-0423	C-32
142-0425	A-93
142-0426	A-78, A-92, H-8
142-0430	C-32
142-0431	C-32
142-0432	C-32
142-0433	C-32
142-0434	C-32
142-0435	C-32
142-0436	C-32
142-0437	C-32
142-0438	C-32
142-0439	C-32
142-0440	C-32
142-0441	C-32
142-0442	C-32
142-0443	C-32
142-0444	C-32
142-0445	C-32
142-0447	C-32
142-0448	C-32
142-0449	C-32
142-0450	C-32
142-0455	A-77

144

144-022	C-39
---------	------

147

147-104	E-53, G-34
147-276	E-54, G-34
147-277	G-34
147-307	G-34
147-311	G-34
147-314	E-53, G-34

147-333	G-34
---------	------

147-2000	E-53, G-34
----------	------------

151

151-099M	G-38
----------	------

153

153-054	C-39
---------	------

163

163-172	A-92
---------	------

171

171A-	D-51, D-53
171B-	D-51, D-53
171C-	D-51, D-53
171D-	D-51, D-53
171E-	D-50, D-52
171F-	D-50, D-52
171G-	D-50, D-52

172

172E-	D-50
172F-	D-50
172G-	D-50

173

173A-	D-51, D-53
173B-	D-51, D-53
173C-	D-51, D-53
173D-	D-51, D-53

180

180-893	B-38
180-896	A-81

182

182-621	B-36
182-624	A-83
182-683	A-89, B-39
182-685	A-82, A-89, B-39

184

184-040	A-81, A-90, H-10
184-041	H-10
184-042	H-10
184-052	H-10
184-105	C-41
184-112	H-10
184-113	A-81, A-90, H-10
184-114	C-41, H-10
184-115	H-10
184-116	A-81, A-90, H-10
184-117	C-41, H-10
184-118	C-41
184-119	C-41
184-120	B-38
184-130	A-81
184-0001	C-40
184-0002	C-40
184-0003	C-40
184-0004	C-40
184-0005	C-40
184-0006	C-41
184-0014	C-40
184-0015	C-40
184-0018	C-40
184-0028	C-40
184-0034	C-40
184-0036	C-40
184-0041	C-40
184-0048	C-40
184-0120	C-24
184-0121	C-24
184-0122	C-24
184-0123	C-24
184-0124	C-24
184-0125	C-24
184-0126	C-24
184-0127	C-24
184-0128	C-24
184-0129	C-24
184-0340	C-41

Part Number Index

186

186-062	B-38
186-0013	B-34
186-0019	B-34
186-0043	C-26
186-0087	B-34
186-0088	B-34
186-0089	C-26
186-0090	B-34
186-0091	B-34

188

188-159	A-90
188-0024	A-26
188-0030	A-26
188-0031	A-26
188-0033	A-26
188-0034	A-26

189

189-142	C-41, G-39
---------	------------

192

192-069	A-79
192-070	A-80
192-200	A-6
192-201	A-6
192-202	A-6, A-17, A-18
192-203	A-6, A-17, A-18
192-204	A-10, A-18
192-205	A-10, A-18
192-206	A-10
192-207	A-8
192-208	A-8, A-18
192-209	A-8
192-210	A-8
192-220	A-6
192-221	A-6
192-222	A-6, A-18
192-223	A-6, A-18
192-224	A-10, A-18
192-225	A-10, A-18
192-226	A-10

192-227	A-8
192-228	A-8, A-18
192-229	A-8
192-230	A-8
192-250	A-6
192-252	A-6
192-254	A-6, A-8, A-12, A-14
192-256	A-6, A-8, A-12, A-14
192-257	A-6, A-8, A-12, A-14
192-258	A-8, A-12, A-14
192-260	A-8, A-12, A-14
192-262	A-10
192-264	A-10
192-265	A-6
192-266	A-6
192-267	A-8, A-12, A-14
192-268	A-8, A-12, A-14
192-269	A-10
192-270	A-10
192-271	A-10
192-300	A-80
192-301	A-82
192-307	A-82, B-36
192-308	A-82, B-37
192-320	A-83
192-321	A-86
192-350	A-6
192-352	A-6
192-354	A-6, A-8, A-12, A-14
192-356	A-6, A-8, A-12, A-14
192-357	A-6, A-8, A-12, A-14
192-358	A-8, A-12, A-14
192-360	A-8, A-12, A-14
192-362	A-10
192-364	A-10
192-365	A-6
192-366	A-6
192-367	A-8, A-12, A-14
192-368	A-8, A-12, A-14
192-369	A-10
192-370	A-10
192-371	A-10
192-478	A-87, A-89, B-39

192-479	A-89, B-39
192-480	A-79, A-89, B-39
192-481	A-81
192-482	A-79, A-89, B-39
192-483	A-80
192-484	A-80
192-485	A-86
192-486	A-86
192-487	A-86
192-488	A-86
192-498	A-79, A-89, B-39
192-499	A-79, A-89, B-39
192-501	A-86
192-502	A-81
192-505	A-81
192-506	B-36
192-507	A-82, B-36
192-525	A-86
192-536	A-86
192-600	A-81
192-623	A-93
192-632	A-78
192-633	A-92
192-644	A-82
192-648	A-80
192-729	A-84
192-730	A-84
192-731	A-84
192-732	A-84
192-734	A-84, G-38
192-735	A-84
192-750	A-81
192-755	A-81
192-759	A-78, A-92
192-773	A-8
192-775	A-85
192-776	A-85
192-777	A-85
192-778	A-85
192-779	A-85
192-780	A-85
192-783	A-85
192-784	A-85

Part Number Index

192 (Continued)

192-840 A-16, A-17, A-18
192-841 A-16, A-17, A-18
192-850 A-16, A-18
192-851 A-16, A-18
192-860 A-84
192-861 A-84
192-868 A-83
192-875 A-89, B-39
192-3044 A-16, A-18
192-3054 A-16, A-18
192-3084 A-16, A-18
192-3144 A-16, A-18
192-3154 A-16, A-18
192-3184 A-16, A-18

193

193-211 A-12
193-212 A-12
193-213 A-12
193-214 A-12
193-215 A-12
193-216 A-12
193-217 A-12
193-218 A-12
193-219 A-14
193-220 A-14
193-231 A-12
193-232 A-12
193-233 A-12
193-234 A-12
193-235 A-12
193-236 A-12
193-237 A-12
193-238 A-12
193-239 A-14
193-240 A-14

194

194-2042 A-17
194-2043 A-17
194-2052 A-17

194-2053 A-17
194-2082 A-17
194-2083 A-17
194-3042 A-16, A-17
194-3043 A-16, A-17
194-3052 A-16, A-17
194-3053 A-16, A-17
194-3082 A-16, A-17
194-3083 A-16, A-17
194-3142 A-16
194-3143 A-16

195

195-066 C-40
195-067 C-40
195-082 C-40
195-098 C-39
195-099 C-39
195-100 C-39
195-108 C-39
195-114 C-40
195-130 C-39
195-0003 C-28
195-0011 C-20
195-1000 C-20
195-2000 C-22

201

201-1000 H-4

240-248

240- D-16
241- D-16
242- D-16
243- D-16
243-0001 G-24
243-0009 C-28, G-18
243-0010 G-20
243-0011 G-22
243-0018 G-28
243-0019 G-30
243-0020 G-32

243-0024 G-26
244- D-16
245- D-16
246- D-17
247- D-17
248- D-16

254-256

254- D-18
255- D-18
256- D-19, D-21
256-1015 C-36

257-258

257- D-19, D-21
258- D-19, D-21

259

259- D-20, D-22

260-265

260- D-20, D-22
261- D-20, D-22
262- D-20, D-22
264- D-20, D-22
265- D-20, D-22
265-060 G-39
265-061 G-39
265-062 G-39
265-1001 G-16
265-1002 G-16
265-1003 G-16
265-1004 G-16
265-1005 G-16
265-1006 G-16
265-1007 G-16
265-1008 G-16

266-268

266- D-20, D-22
268- D-23, D-26, D-29

Part Number Index

269

269	D-29
269-062	C-28, C-41
269-1066	C-34
269-1067	C-34
269-1068	C-34
269-1069	C-34
269-1200	G-10

270-276

270-	D-23, D-26, D-29
271-	D-25, D-28, D-31
272-	D-25, D-28, D-31
273-	D-25, D-28, D-31
274-	D-24, D-27, D-30, D-33, D-36, D-39, D-40, D-41, D-43, D-46, D-49
275-	D-25, D-28, D-31, D-34, D-37, D-39, D-44, D-47, D-49
276-	D-24, D-27, D-30, D-33, D-36, D-39, D-43, D-46, D-49

277-284

277-	D-23, D-26, D-29, D-32, D-35, D-38, D-42, D-45, D-48
278-	D-26, D-35, D-45
279-	D-32, D-35, D-38, D-42, D-45, D-48
281-	D-32, D-35, D-38, D-42, D-45, D-48
283-	D-23, D-26, D-29, D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48
284-	D-26, D-35, D-45

285-299

285-	D-32, D-35, D-38, D-42, D-45, D-48
287-	D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48
289-	D-33, D-36, D-39, D-43, D-46, D-49

290-	D-34, D-37, D-44, D-47, D-49
291-	D-24, D-27, D-30, D-33, D-36, D-39, D-43, D-46, D-49

292-	D-33, D-36, D-39, D-43, D-46, D-49
------	---------------------------------------

293-	D-34, D-37, D-39, D-44, D-47, D-49
------	---------------------------------------

294-	D-33, D-36, D-40, D-41, D-43, D-46, D-49
------	--

296-	D-39
------	------

298-	D-24, D-27, D-30
------	------------------

299-	D-24, D-27, D-30
------	------------------

331

331-004	E-51
331-005	E-51
331-006	E-51
331-033	E-51
331-293	E-51
331-434A	E-52
331-535	E-50
331-547	E-54
331-618	E-52
331-623	E-51
331-623A	E-51
331-631	E-53
331-632	E-53
331-653	E-51
331-657	E-50
331-671	E-51
331-674	E-52
331-805	E-50
331-807	E-51
331-862	E-54
331-916	E-51
331-938	E-54
331-939	E-54
331-941	E-50
331-947	E-50, D-225
331-958	E-50, D-225
331-2793	E-40

331-2794	E-40
331-2856	E-40
331-2857	E-40
331-2858	E-40
331-2882	E-44
331-2904	E-38
331-2905	E-38
331-2906	E-38
331-2909	E-38
331-2910	E-38
331-2911	E-38
331-2917	E-38
331-2927	E-38
331-2929	E-38
331-2930	E-38
331-2931	E-38
331-2934	E-38
331-2961	E-38
331-2963	E-38
331-2966	E-38
331-2968	E-38
331-2973	E-38
331-2974	E-38
331-2988	E-40
331-3000	E-38
331-3001	E-38
331-3002	E-38
331-3004	E-38
331-3011	E-40
331-3012	E-40
331-3013	E-40
331-3015	E-38
331-3016	E-38
331-3017	E-38
331-3018	E-38
331-3019	E-38
331-3060	E-40
331-3070	E-42
331-4310	E-36
331-4311	E-36
331-4312	E-36
331-4313	E-36

Part Number Index

331 (Continued)

331-4314	E-36
331-4331	E-36
331-4510	E-36
331-4511	E-36
331-4512	E-36
331-4513	E-36
331-4514	E-36
331-4531	E-36
331-4810	E-36
331-4811	E-36
331-4812	E-36
331-4813	E-36
331-4814	E-36
331-4831	E-36

332

332-2856	E-40
332-3011	E-40
332-2973	E-38
332-3107	E-38
332-4531	E-36
332-4811	E-36
332-4831	E-36

333

333-030	E-52
333-043-03	E-53
333-045	E-54
333-056	E-54
333-071	E-54
333-072	E-54
333-078	E-50
333-148	E-52
333-176	E-51
333-181	E-50
333-182	E-50
333-183	E-50
333-184	E-53
333-194	E-53
333-197	E-54

333-207	E-51
333-208	E-52
333-572	E-54

338

338-031	E-55
338-041 thru 046	E-47

356

356-090	A-92
356-115	A-91, A-92
356-0012	A-22
356-0013	A-22
356-0750	A-22
356-1005	A-22
356-1006	A-22

357-358

357-001	A-91, A-92
357-0001	A-24
357-0003	A-24
357-0004	A-24
357-0005	A-24
358-051	A-93

380

380-024	H-18
---------------	------

403-443

403-007	A-92
410455758	D-230
410455828	D-230
410456348	D-230
411555648	D-224
426855048	D-230
426855108	D-230
426888950	D-223
443155438	D-230

466

466856418	D-230
466856668	D-230
466857488	D-230
466857518	D-230

531-535

531-833	A-77, C-39, G-38, H-18
533-376	B-14
533-377	B-14
533-380	B-14
535-490	B-14

536

536-376	B-30
536-378	B-30
536-380	B-30
536-382	B-30
536-384	B-30
536-666	B-37
536-767	B-14
536-768	B-14
536-774	B-14
536-780	B-14
536-983	B-4
536-984	B-6
536-994	B-6

540

540-142	B-37
540-984	B-6
540-995	B-6

Part Number Index

544

544-023	D-223, D-225
544-374	B-6
544-459	H-19
544-560	B-14
544-562	B-14
544-782	B-36
544-783	B-36
544-784	B-36
544-785	B-36
544-973	B-6

545

545-113	G-36
545-208	G-36

567

567-176B	H-19
567-225	H-19
567-334	H-19
567-335	H-19
567-351	H-16
567-352	H-16
567-353	H-16
567-361	H-16
567-362	H-16
567-363	H-16
567-371	H-16
567-372	H-16
567-373	H-16
567-381	H-16
567-382	H-16
567-383	H-16
567-390	H-16
567-391	H-16

590

590-500	B-37
590-501 thru 510	B-22
590-780 thru 782	B-22

599

599-00210 thru 00214	D-16, D-17, D-68
599-00230 thru 00234	D-16, D-17, D-68
599-00423	D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48, D-131, D-139, D-225, G-34
599-00426	D-23, D-26, D-29, D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48, D-121, D-126, D-131, D-139, D-225, G-34
599-00436	D-231
599-00510 thru 00514	D-16, D-17, D-68
599-00530 thru 00534	D-16, D-17, D-68
599-00599	D-223
599-01000	D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48, D-131, D-134, D-139, D-146
599-01010	D-32, D-35, D-38, D-42, D-45, D-48, D-131, D-139
599-01050	D-23, D-26, D-29, D-32, D-35, D-38, D-40, D-41, D-42, D-45, D-48, D-121, D-126, D-131, D-134, D-139, D-144
599-01051	D-26, D-35, D-45, D-121, D-126, D-131, D-139, D-144
599-01060 thru 01061	D-230
599-01070	D-230
599-01081	D-23, D-26, D-29, D-121, D-126, D-142
599-01082 thru 01083	D-29, D-121, D-126, D-142
599-01088	D-19, D-21, D-98, D-103
599-01093	D-230
599-01100 thru 01131	D-18, D-86
599-01132 thru 01139	D-18, D-90
599-02000 thru 02029	D-19, D-20, D-97

599-02030 thru 02063	D-19, D-20, D-97
599-02064 thru 02079	D-21, D-22, D-102
599-02941	D-223
599-02942	D-223
599-03000 thru 03008	D-26, D-27, D-28, D-119
599-03009 thru 03014	D-119
599-03015 thru 03017	D-119
599-03018 thru 03026	D-26, D-27, D-28, D-119
599-03027 thru 03032	D-119
599-03033 thru 03035	D-119
599-03054 thru 03062	D-26, D-27, D-28, D-120
599-03063 thru 03068	D-120
599-03069 thru 03071	D-120
599-03072 thru 03080	D-26, D-27, D-28, D-120
599-03081 thru 03086	D-120
599-03087 thru 03089	D-120
599-03108 thru 03116	D-23, D-24, D-25, D-119
599-03117 thru 03122	D-119
599-03123 thru 03125	D-119
599-03126 thru 03134	D-23, D-24, D-25, D-119
599-03135 thru 03140	D-119
599-03141 thru 03143	D-119
599-03144 thru 03152	D-29, D-30, D-31, D-125
599-03153 thru 03161	D-125
599-03162 thru 03170	D-23, D-24, D-25, D-118
599-03171 thru 03179	D-118
599-03180 thru 03188	D-23, D-24, D-25, D-118
599-03189 thru 03194	D-118
599-03195 thru 03197	D-118
599-03198 thru 03206	D-29, D-30, D-31, D-125
599-03207 thru 03212	D-125

Part Number Index

599 (Continued)

599-03213 thru 03215 D-125
599-03216 thru 03221 D-119
599-03225 thru 03230 D-119
599-03234 thru 03239 D-120
599-03243 thru 03248 D-120
599-03252 thru 03257 D-119
599-03261 thru 03266 D-119
599-03270 thru 03276 D-118
599-03279 thru 03284 D-118
599-03300 thru 03344 D-226
599-03345 thru 03389 D-227
599-03390 thru 03391 D-227
599-03394 thru 03396 D-232
599-03609 D-24, D-27, D-30,
D-121, D-126, D-156
599-03610 D-225
599-03611 D-24, D-27, D-30,
D-121, D-126, D-156
599-05011 thru 05020 D-231
599-05920 thru 05924 D-42, D-43,
D-44, D-130
599-05930 thru 05934 D-42, D-43,
D-44, D-130
599-05940 thru 05944 D-42, D-43,
D-44, D-130
599-05950 thru 05954 D-42, D-43,
D-44, D-130
599-05960 thru 05964 D-32, D-33,
D-34, D-130
599-05970 thru 05974 D-32, D-33,
D-34, D-130
599-05980 thru 05984 D-32, D-33,
D-34, D-130
599-05990 thru 05994 D-32, D-33,
D-34, D-130
599-06040 thru 06044 D-35, D-36,
D-37, D-131
599-06050 thru 06054 D-35, D-36,
D-37, D-131
599-06060 thru 06064 D-35, D-36,
D-37, D-131

599-06070 thru 06074 D-35, D-36,
D-37, D-131
599-06120 thru 06124 D-45, D-46,
D-47, D-131
599-06130 thru 06134 D-45, D-46,
D-47, D-131
599-06140 thru 06144 D-45, D-46,
D-47, D-131
599-06150 thru 06154 D-45, D-46,
D-47, D-131
599-06160 thru 06164 D-38, D-39,
D-138
599-06165 thru 06169 D-38, D-39,
D-138
599-06170 thru 06174 D-48, D-49,
D-138
599-06175 thru 06179 D-48, D-49,
D-138
599-06610 thru 06629 D-134
599-08020 thru 08021 D-229
599-09144 thru 09148 D-231
599-09181 thru 09190 D-232
599-09201 thru 09209 D-226
599-09210 thru 09212 D-227
599-09213 thru 09218 D-226
599-09219 thru 09230 D-227
599-09236 thru 09245 D-231
599-10048 thru 10049 D-230
599-10065 D-225
599-10071 D-225
599-10077 D-223, D-224
599-10078 D-224
599-10100 thru 10119 .. D-228, D-229
599-10120 thru 10129 D-229
599-10130 thru 10149 D-228
599-10200 D-231
599-10203 thru 10225 D-50, D-51
599-10250 thru 10267 D-52, D-53

656

656-014 D-234
656-599 thru 601 D-234
656-736 D-223, D-234
656-761 thru 762 D-234
656-764 thru 766 D-234
656-768 D-234
656-830 thru 834 D-234
656-0001 D-234
656-0002 D-55, D-196, D-234
656-0003 D-234
656-0004 D-55, D-196, D-234
656-0005 D-234
656-0009 thru 0010 D-55, D-198,
D-234, H-4
656-0011 D-55, D-198, D-234
656-0012 D-55, D-196, D-234
656-0013 thru 0015 D-234
656-0017 thru 0019 D-55, D-200,
D-234
656-0020 D-234
656-0021 D-53, D-192, D-234
656-0022 D-234
656-0028 thru 0029 D-234

658

658-067 thru 072 D-235
658-074 D-235
658-166 thru 167 D-235
658-376 D-235
658-379 D-235
658-405 thru 408 D-235
658-0001 thru 0002 D-235
658-0004 thru 0005 D-56, D-202,
D-235
658-0007 thru 0008 D-56, D-206,
D-235
658-0009 D-235

Part Number Index

658-0010	D-56, D-206	814	985-008P20	E-48
658-0011	D-235	814-018	985-035P25	E-48
658-0012	D-56, D-206		985-047	E-46
658-0013	D-235	832-833	985-051P10	E-48
658-0014	D-56, D-206	832-034	985-052P20	E-48
658-0018 thru 0022	D-235	832-040	985-053P48	E-48
658-0026 thru 0033	D-235	832-164	985-054P24	E-46
658-0043	D-56, D-202, D-235	832-177	985-055P24	E-48
658-0050 thru 0052	D-56, D-204, D-235	832-178	985-092	E-48
658-0064 thru 0071	D-56, D-206, D-235	832-179	985-093	E-48
658-0085 thru 0086	D-56, D- D-235	832-0120	985-094P10	E-48
658-0100 thru 0101	D-235	832-0490	985-098P10	E-46
		832-0500	985-101P25	E-48
		832-1260	985-106	E-49
		833-033	985-105	E-49
			985-107	E-49
698		856	985-108	E-49
698-088	D-223	856-036	985-124	E-49
		856-044	985-131	E-49
746		856-046	985-133	E-49
74 662 0068 0	B-38	856-055	985-134	E-49
			985-135	E-49
786		894	985-241P20	E-48
786-062	G-38	894-368	985-242P20	E-48
786-131	G-38			
786-0600	G-4	908		
786-0610	G-4	908-033	994-809	F-22
		908-042	994-975	F-22
7MF		908-051	994-976	F-22
7MF15644BA003EA1 thru		908-052	994-977	F-22
7MF15644CD103EA1	B-24		994-978	F-22
		985		
808		985-003		
808-412	A-92	985-004		
808-517	A-90, A-91, H-18	985-006		

Part Number Index

ACS

ACS100.1U.....C-38

AQB

AQB22.1.....B-37

AQB51.1.....B-37

AQE

AQE2000.....B-38

AQF

AQF3050.....B-37

AQF3100.....B-20, B-38

AQF3101.....B-37

AQF3150.....B-37

AQF4150.....B-37

AQY

AQY2010.....B-20

AQY2030.....B-20

ARG

ARG62.21.....C-38

ARG70.....A-56, A-77

ARG100.....C-38

ARG150U.....C-38

ARG70.....A-77

ARK

ARK10 – ARK21.....D-222, D-225

ASC

ASC1.6.....D-224

ASC9.3BCU.....D-224

ASC9.3DU.....D-224

ASC9.4U.....D-224

ASC77.2U.....E-49

ASE

ASE1 thru ASE2.....D-233

ASE12.....D-233

ASK

ASK50 thru ASK51.....D-231

ASK71.11.....E-47

ASK71.1U.....E-47

ASK71.2U.....E-47

ASK71.13.....E-46

ASK71.3.....E-46

ASK71.14.....E-46

ASK71.4.....E-46

ASK71.5.....E-46

ASK71.6.....E-46

ASK71.9.....E-46

ASK73.1.....E-47

ASK73.2U.....E-47

ASK74.1U.....E-48

ASK75.1U.....E-49

ASK75.3U.....E-49

ASK76.1U.....E-48

ASK78.3U.....E-48

ASK79.165.....E-28

ASK79.212.....E-28

ASK79.250.....E-28

ASK79.350.....E-28

ASY-ASZ

ASY8L15.....D-223

ASY8L45.....D-223

ASY97 – ASY100.....D-223

ASZ7.3.....D-224

BSG

BSG21.1.....C-38

BSG61.....E-49

BV2-BV3

BV2W-.....D-57, D-60, D-62
D-210

BV3W-.....D-58, D-59, D-61,
D-63, D-64, D-210

BYA-BYE

BYAxxx.....F-11, F-19

BYExxx.....F-15

GBB

GBB131.....E-24

GBB132.....E-24

GBB136.....E-24

GBB161.....E-24

GBB163.....E-24

GBB164.....E-24

GBB166.....E-24

GCA

GCA16x.....A-52

GCA121.....E-12

GCA126.....E-12

GCA131.....E-12

GCA132.....E-12

GCA136.....E-12

GCA151.....E-12

GCA156.....E-12

GCA161.....E-12

GCA163.....E-12

GCA164.....E-12

GCA166.....E-12

GCA221.....E-12

GCA226.....E-12

Part Number Index

GDE

GDE131	E-16
GDE132	E-16
GDE136	E-16
GDE161	A-56, E-16
GDE163	E-16
GDE164	E-16
GDE166	E-16

GEB

GEB131	E-22
GEB132	E-22
GEB161	E-22
GEB164	E-22

GGD

GGD121	E-32
GGD221	E-32
GGD321	E-32

GIB

GIB131	E-26
GIB132	E-26
GIB136	E-26
GIB161	E-26
GIB163	E-26
GIB164	E-26
GIB166	E-26

GLB

GLB16x	A-52
GLB131	E-20
GLB132	E-20
GLB136	E-20
GLB161	A-56, E-20
GLB163	E-20
GLB164	E-20
GLB166	E-20

GMA

GMA121	E-8
GMA126	E-8
GMA131	E-8
GMA132	E-8
GMA136	E-8
GMA151	E-8
GMA156	E-8
GMA161	A-56, E-8
GMA163	E-8
GMA164	E-8
GMA166	E-8
GMA221	E-8
GMA226	E-8

GND

GND121	E-28
GND126	E-28
GND221	E-28
GND226	E-28
GND321	E-28
GND326	E-28

GQD

GQD121	E-4
GQD131	E-4
GQD151	E-4
GQD221	E-4

M3P

M3P80FY	D-54, D-180
M3P100FY	D-54, D-180
M3P80FY/2BN	D-54, D-180
M3P100FY/2BN	D-54, D-180
M3P80PY/3BN	D-54, D-180
M3P100FY/3BN	D-54, D-180

MVF

MVF461H15-0.6	D-54, D-185
MVF461H15-1.5	D-54, D-185
MVF461H15-3	D-54, D-185
MVF461H20-5	D-54, D-185
MVF461H25-8	D-54, D-185
MVF461H32-12	D-54, D-185
MVF461H40-20	D-54, D-185
MVF461H50-30	D-54, D-185

MXF

MXF461.65-50U	D-54, D-176
---------------	-------------

MXG

MXG461B15-0.6	D-54, D-189
MXG461B15-1.5	D-54, D-189
MXG461B15-3	D-54, D-189
MXG461B20-5	D-54, D-189
MXG461B25-8	D-54, D-189
MXG461B32-12	D-54, D-189
MXG461B40-20	D-54, D-189
MXG461B50-30	D-54, D-189
MXG461.15-0.6U	D-54, D-176
MXG461.15-1.5U	D-54, D-176
MXG461.15-3.0U	D-54, D-176
MXG461.20-5.0U	D-54, D-176
MXG461.25-8.0U	D-54, D-176
MXG461.32-12U	D-54, D-176
MXG461.40-20U	D-54, D-176
MXG461.50-30U	D-54, D-176

QAA

QAA	B-8
QAA20	B-10
QAx20	B-12

QAD-QAE

QAD20xx.xxxx	B-20
QAE20xx.xxxx	B-20

Part Number Index

QAH

QAH11.1A-68, A-77

QFA

QFA2000 B-16

QFA2001 B-16

QFA2060 B-16

QFA2071 B-16

QFA3000 B-16

QFA3001 B-16

QFA3060 B-16

QFA3071 B-16

QFA3100 B-20

QFA3101 B-20

QFA3160 B-20

QFA3171 B-20

QFA4160 B-20

QFA4171 B-20

QFM

QFM2100..... B-18

QFM2101..... B-18

QFM2110..... B-18

QFM2120..... B-18

QFM2160..... B-18

QFM2171..... B-18

QFM3100..... B-18

QFM3101..... B-18

QFM3160..... B-18

QFM3171..... B-18

QFM4101..... B-18

QFM4160..... B-18

QFM4171..... B-18

QPA

QPA2000 B-26

QPA2002 B-26

QPA2060 B-26

QPA2062 B-26

QPM

QPM2100 B-28

QPM2102 B-28

QPM2160 B-28

QPM2162 B-28

QVM

QVM62.1 B-32

RAA

RAA10 A-34

RAA20 A-34

RAB

RAB10 A-38

RAB20 A-38

RAB30 A-38

RAB90 A-38

RCC

RCC10U A-42

RCC20U A-42

RCC30U A-44

RCU

RCU15U A-48

RCU50U A-48

RCU61U A-52

RDF

RDF10U..... A-68

RDF20U..... A-68

RDF50.1U..... A-68

RDF60.1U..... A-68

RDU

RDU20U A-60

RDU50U A-60

RDX

RDX42 A-64

RLA

RLA162.5U A-56

RLM

RLM162U A-56

RWD

RWD44U C-8

RWD45U C-8

RWD62U C-4

RWD68U C-4

RWD82U C-4

SED

SED2- F-6

SED2-AOP1 F-26

SED2-BACNET F-27

SED2-BOP1 F-26

SED2-DOOR-KIT1 F-26

SED2-DOOR-KIT2 F-26

SED2-EASYCOMM F-26

SED2-GL-A F-26

SED2-GL-B F-26

SED2-GL-C F-26

SED2-LONI/F F-27

SED2-MODBUS2 F-27

SED2-MODBUS_KIT F-27

SED2-PC-KIT F-26

SED2-PS-A F-26

SED2-PS-B F-26

SED2-PS-C F-26

SED2-PS-DE F-26

Part Number Index

SEH-SEM

SEH62.1U..... C-12, C-38
SEM62.2U C-14, C-38

SEZ

SEZ220..... C-16
SEZ91.6..... D-233

SFA-SFP

SFA11U D-16, D-68, D-72
SFA71U D-16, D-68, D-72
SFP11U D-16, D-68, D-72
SFP71U D-16, D-68, D-72

SKB-SKD

SKB62U..... D-24, D-27, D-30,
D-33, D-36, D-39,
D-43, D-46, D-126,
D-131, D-160
SKB62UA..... D-160
SKB82.50U..... D-34, D-37, D-39,
D-44, D-47, D-49
D-131, D-139, D-162
SKB82.51U..... D-33, D-36, D-39,
D-43, D-46, D-49,
D-131, D-139, D-162
SKC62U..... D-33, D-36, D-39,
D-40, D-41, D-43,
D-46, D-49, D-131, D-160
SKC62UA D-160
SKC82.60U..... D-34, D-37, D-39,
D-42, D-45, D-47,
D-131, D-162
SKC82.61U..... D-33, D-36, D-39,
D-41, D-44, D-47,
D-129, D-162
SKD62U..... D-24, D-27, D-30,
D-33, D-36, D-39,
D-40, D-41, D-44,
D-47, D-121,
D-131, D-152
SKD62UA D-152

SKD82.50U..... D-25, D-28, D-31,
D-34, D-37, D-39,
D-44, D-47, D-121,
D-126, D-131, D-154

SKD82.51U..... D-24, D-27, D-30,
D-33, D-36, D-39,
D-43, D-46, D-126,
D-131, D-154

SQS-SQX

SQS65U D-20, D-22, D-98,
D-103, D-112,
SQS65.5U D-20, D-22, D-95,
D-98, D-103, D-112
SQS85.53U D-20, D-22,
D-98, D-103, D-114
SQX62U D-25, D-28,
D-121, D-126
SQX82.00U D-25, D-28, D-31,
D-121, D-126, D-150
SQX82.03U D-25, D-28, D-31,
D-121, D-126, D-150

SSA-SSP

SSA61U..... D-16, D-66, D-76
SSA81U..... A-52, D-16, D-68, D-76

SSB-SSC

SSB61U..... A-52, D-18,
D-84, D-88, D-90
SSB81 A-52
SSB81U..... D-18, D-84,
D-88, D-92
SSC61U..... D-20, D-22,
D-98, D-103, D-110
SSC61.5U..... D-20, D-22,
D-98, D-103, D-110
SSC81 A-52
SSC81U..... D-20, D-22,
D-98, D-103
SSC81.5U..... D-20, D-22,
D-98, D-103

SSP

SSP61U..... D-16, D-68, D-76

STA-STP

STA71..... D-17, D-68, D-80
STP71..... D-17, D-68, D-80

VBA-VBE

VBAxxx F-11, F-21
VBExxx F-17

Z-ZM

Z56/100 D-233
Z205/15 thru Z205/100 D-233
Z206/15 thru Z206/50 D-233
Z366 D-233
ZM100/A..... D-192, D-232
ZM101/A..... D-192, D-232
ZM110..... D-192, D-232
ZM111 D-192, D-232
ZM120/A..... D-192, D-232
ZM121/A..... D-192, D-232
ZM150 D-192, D-232
ZM200/A..... D-192, D-232
ZM210 D-192, D-232
ZM220/A..... D-192, D-232
ZM250 D-232

Subject Index

Sorted by Subject

A

Airflow Switches, Differential Static Pressure.....	G-11
Air Station Equipment.....	H-3
Air Velocity Sensor.....	B-31
Analog Relays—Pneumatic.....	G-21
Analog Sensors, 4-20mA 100K NTC/Platinum.....	B-13
Angle/Flared/Sequence/Changeover Service Valves.....	D-193 – D-205
Auxiliary Equipment Accessories & Service Kits.....	H-17

B

Balance-retard Relays, Pneumatic.....	G-19
Ball Valves	
Application Matrix.....	D-5
Flow Coefficients.....	D-15
Selection Tables.....	D-50 – D-53
Specifications & Ordering.....	D-163 – D-165
Butterfly Valves	
Application Matrix.....	D-5
Selection Tables.....	D-57 – D-64
Specifications & Ordering.....	D-207 – D-209
Button Room Temperature Sensors.....	B-7

C

CO ₂ /VOC Sensors	
Duct.....	B-27
Room.....	B-25
Controllers/Room Thermostats, Electric	
Fan Coil Thermostats.....	A-37
Line Voltage Remote Bulb Thermostats.....	A-29
Line Voltage Room Thermostats – Heating/Cooling.....	A-31
Room Temperature Controller for CAV and VAV Systems.....	A-51
Room Temperature Controller with LCD for Heating and Cooling Systems.....	A-59
Room Thermostats.....	A-33
Control Panels.....	H-15
Conversion Charts and Tables	
Conversion Factors.....	I-23
English to Metric Conversions.....	I-25
Pressure Conversions.....	I-26
Psychrometric Chart.....	I-28
Temperature Conversions.....	I-27

D

“D” Series Pneumatic Room Thermostats.....	A-19
Damper Actuators	
Accessories & Service Kits.....	E-45
Electronic Spring Return.....	E-3 – E-11
Electronic Spring Return for UL Listed Fire/Smoke Control Dampers.....	E-27 – E-31
Large Capacity, Pneumatic.....	E-43
Non-spring Return.....	E-15 – E-25
Overview & Selection Guide.....	E-2
Part. No. Nomenclature.....	E-34
Pneumatic Spring Return.....	E-35 – E-40
Tandem Mounting, Pneumatic.....	E-41
Duct Limitem Thermostats, Pneumatic	
Remote Bulb.....	A-23
Rigid Bulb.....	A-21

Duct Sensors

CO ₂	B-27
CO ₂ /Temperature.....	B-27
CO ₂ /VOC.....	B-27
Relative Humidity & Temperature, Electric.....	B-17

E

Electric Room Thermostats/Controllers

Fan Coil.....	A-37
Free Energy Band Controllers for Four-Pipe Fan Coil Units.....	A-43
Line Voltage Remote Bulb.....	A-29
Line Voltage, Heating/Cooling.....	A-31
Low Temperature Detection.....	A-73
Room.....	A-33
Room Temperature Controllers for CAV Systems.....	A-47
Room Temperature Controllers for CAV and VAV Systems.....	A-51
Room Temperature Controllers for Two-Pipe Fan Coil Units.....	A-41
Room Temperature Controllers with LCD.....	A-63
Room Temperature Controllers with LCD for Heating and Cooling Systems.....	A-59
Room Temperature Controllers with LCD for Two-Pipe Fan Coil Units.....	A-67
Room Temperature Controllers with Two 0 to 10 Vdc Outputs.....	A-55
Surface Mounted/High Temperature Limit Control....	A-71

Subject Index

Electric Thermostats for Specialized Applications	A-71 – A-73
Electro-Mechanical Rack and Pinion Actuator	D-155
Electronic Damper Actuators	
Accessories & Service Kits	E-45
Non-spring Return	E-15 – E-25
Spring Return	E-3 – E-11
Spring Return for UL Listed Fire/Smoke Control Dampers	E-27 – E-31
Overview & Selection Guide	E-2
Part. No. Nomenclature.....	E-34
Electronic Sensors	
4-20 mA Signal Analog.....	B-13
10K Ohm (Type II) Thermistor.....	B-5
100K NTC Room Temperature.....	B-3
Air Velocity	B-31
Analog	B-13
Button Room Temperature	B-7
Duct Carbon Dioxide and Carbon Dioxide/Temperature.....	B-27
Duct, Pipe and Outdoor Air Temperature	B-11
Duct Relative Humidity and Relative Humidity/Temperature.....	B-17
Flush Mount Room Temperature.....	B-5
Outside Air Relative Humidity and Relative Humidity/Temperature.....	B-19
Pitot Tube Kits	B-29
Pressure Sensor for Liquid and Gas	B-23
Room Carbon Dioxide.....	B-25
Room Relative Humidity and Relative Humidity/Temperature.....	B-15
Very Low Differential Pressure Transducers	B-21
Electronic Temperature Controllers	
Heat Pump	C-7
Refrigeration.....	C-7
Signal Converter	C-15
Time Clock	C-11
Transformer.....	C-13
Universal	C-3
Electronic-to-Pneumatic Transducer	G-35
Engineering Information	
Butterfly Valve Selection and Sizing.....	I-14
Control Valve Selection and Sizing	I-2
Conversion Factors	I-23
Damper Actuator Sizing	I-17
Globe and Ball Valves Sizing	I-2
NEMA Descriptions	I-18
Pneumatic Relays	I-19
Psychrometric Chart.....	I-28
Enthalpy Control Switch, Electric	G-7
EP Valve, Three-way	G-15
External Restrictors	H-9
F	
Fan Coil Thermostats	
Electric	A-37
Free Energy Band Room Temperature Controller....	A-43
Room Temperature Controller for Two-Pipe Fan Coil Units	A-41
Flared Valves for Specialized Applications	D-195
G	
Gauges	
Pressure.....	H-7
Receiver	C-31
Globe Valves	
Application Matrix.....	D-5
Close-off Pressure	D-12
Flowrite Series Specifications & Ordering.....	D-115 – D-161
High Pressure Close-off.....	D-133
MT Series Specifications & Ordering	D-95 – D-114
MZ Series Specifications & Ordering	D-85 – D-94
Powermite Series Specifications & Ordering	D-83 – D-113
Selection Tables	D-18 – D-49
Steam Capacity.....	D-10
Temperature Pressure Ratings	D-11
Water Capacity.....	D-8
HIJK	
Heat Pump Temperature Controller	C-7
Highest Pressure Signal Selector	G-27
Hygrostats, Room and Duct	B-33

Subject Index

L

Limitem, Pneumatic Thermostat

- Remote Bulb A-23
- Rigid Bulb..... A-21

Line Voltage Electric Thermostats

- Remote Bulb A-29
- Room-Heating/Cooling A-31

Low Differential Pressure Transmitters, Pneumatic C-27

Low Temperature Detection Thermostats, Electric..... A-73

Lowest and Highest Signal Selector..... G-29

Lowest Pressure Signal Selector G-31

M

Magnetic Valves

- Application Matrix..... D-5
- Selection Tables D-54
- Specifications & Ordering D-173 – D-187
- Terminal Housing D-191

Multiple Input Receiver-Controller, Pneumatic C-21

Multi-purpose Relay G-17

N

NEMA Ratings I-18

P

Panels, Control H-15

Pitot Tube Sensor Kits B-29

Pneumatic Auxiliary Equipment

- Accessories & Service Kits H-17 – H-19
- Air Station Equipment H-3
- External Restrictors H-9
- Pneumatic Tube Fitting Kit H-13
- Pressure Gauges H-7

Pneumatic Damper Actuators

- Accessories & Service Kits E-45
- Large Capacity E-43
- Overview & Selection Guide E-2
- Part. No. Nomenclature..... E-34
- Spring Return E-35 – E-40
- Tandem Mounting..... E-41

Pneumatic Gauges

- Pressure H-7
- Receiver C-31

Pneumatic High and Low Temperature Detection Thermostats A-27

Pneumatic Receiver-Controllers

- Multiple Input..... C-21
- Single Input C-19

Pneumatic Regulators/Controllers

- Static Pressure and Liquid Level Regulators C-33
- Step Controller C-35

Pneumatic Relative Humidity Sensors

- Room and Duct Hygrostats B-33

Pneumatic Relays

- Analog G-21
- Balance-retard..... G-19
- Highest Pressure Signal Selector G-27
- Lowest and Highest Signal Selector G-29
- Lowest Pressure Signal Selector G-31
- Multi-purpose G-17
- Positioning..... G-33
- Reverse Acting G-25

Pneumatic Room and Duct Hygrostats B-33

Pneumatic Transmitters

- Low Differential Pressure C-27
- Room and Duct Humidity C-25
- Temperature C-23

Pneumatic Room Thermostats

D Series

- Room..... A-19

Powerstar

- Day/Night and Day/Night/Vent A-9
- Free Energy Band Heating/Cooling A-11
- Heating/Cooling..... A-7
- (Hesitation) Free Energy Band Heating/Cooling A-13
- Overview/Selection Guide..... A-3
- Retroline® Retrostat Retrofit A-15
- Single Setpoint A-5

Pneumatic Signal Selectors

- Highest Pressure..... G-27
- Lowest and Highest..... G-29
- Lowest Pressure G-31

Subject Index

Pneumatic Thermostats for Specialized Applications

High and Low Temperature Detection	A-27
Limitem Remote Bulb	A-23
Limitem Rigid Bulb	A-21
Unit Mounted	A-25

Pneumatic Tube Fitting Kit

H-13

Pneumatic Transmitters

Low Differential Pressure	C-27
Room and Duct Humidity	C-25
Temperature	C-23

Pneumatic Valve Actuators

Flowrite

4-inch	D-141
8-inch	D-143
12-inch	D-145

Powermite

Two-inch	D-105
----------------	-------

Positioning Relay, Pneumatic

G-33

Positioning Switches, Electric

G-5

Powerstar Room Thermostats

Day/Night and Day/Night/Vent Room Thermostats	A-9
Free Energy Band Heating/Cooling Room Thermostats	A-11
Heating/Cooling Room Thermostats	A-7
(Hesitation) Free Energy Band Heating/Cooling Room Thermostats	A-13
Overview/Selection Guide	A-3
Retroline® Retrostat Retrofit Room Thermostats	A-15
Single Setpoint Room Thermostats	A-5

Powertop 658 Series Valves

Sequence and Changeover	D-203
Two-way	D-201
Two-way Angle Union/Normally Open	D-205

Pneumatic Relays

Relay Piping	I-19
Retrofit Cross Reference	I-22

Pressure Conversion

I-26

Pressure Electric Switches

G-13

Pressure Gauges

H-7

Pressure Sensors, Electronic

Pressure Sensor for Liquid and Gas	B-23
Very Low Differential Pressure Transducers	B-21

Psychrometric Chart

I-28

R

Receiver-Controllers, Pneumatic

Multiple Input	C-21
Single Input	C-19

Receiver Gauges, Pneumatic

C-31

Regulators/Controllers, Pneumatic

Static Pressure and Liquid Level Regulators	C-33
Step Controller	C-35

Relative Humidity/Relative Humidity & Temperature Sensors

Electronic

Duct Relative Humidity and Relative Humidity & Temperature	B-17
Room Relative Humidity and Relative Humidity & Temperature	B-15
Outside Air Relative Humidity and Relative Humidity & Temperature	B-19

Relays, Pneumatic

Analog	G-21
Balance-retard	G-19
Highest Pressure Signal Selector	G-27
Lowest and Highest Signal Selector	G-29
Lowest Pressure Signal Selector	G-31
Multi-purpose	G-17
Positioning	G-33
Relay Piping	I-19
Retrofit Cross Reference	I-22
Reverse Acting	G-25
Switching	G-23

Restrictors, External

H-9

Retroline® Retrostat Retrofit Room Thermostats

A-15

Reverse Acting Relays

G-25

Room and Duct Hygrostats

B-33

Room CO₂ Sensors

B-25

Room Relative Humidity and Relative Humidity & Temperature Sensors, Electric

B-15

Subject Index

R *(Continued)*

Room Thermostats/Controllers, Electric

Fan Coil.....	A-37
Free Energy Band Heating/Cooling for Two-Pipe Fan Coil Units	A-43
Line Voltage Remote Bulb.....	A-29
Line Voltage Room–Heating/Cooling	A-31
Room.....	A-33
Room Temperature Controller for CAV Systems.....	A-43
Room Temperature Controller for Two-pipe Fan Coil Units	A-41
Room Temperature Controller with LCD	A-63
Room Temperature Controller with LCD for Heating and Cooling Systems	A-59
Room Temperature Controller with Two 0 to 10 Vdc Outputs	A-55

Room Thermostats/Controllers, Pneumatic

Room.....	A-19
-----------	------

S

Selector Switches, Electric..... G-3

Sensors, Electronic

4-20 mA Signal Analog.....	B-13
100K NTC Room Temperature.....	B-3
CO ₂ /VOC.....	B-25 – B-27
Duct Carbon Dioxide	B-27
Duct, Pipe and Outdoor Air Temperature	B-11
Duct Relative Humidity and Relative Humidity/Temperature.....	B-17
Metal Flush Mount Room Temperature.....	B-5
Outside Air Relative Humidity and Relative Humidity/Temperature.....	B-19
Pressure Sensor for Liquid and Gas	B-23
Room Carbon Dioxide Sensor	B-25
Room Relative Humidity and Relative Humidity/Temperature.....	B-15
Room Temperature	B-9
Very Low Differential Pressure Transducers	B-21

Sensors, Pneumatic Relative Humidity

Room and Duct Hygrostats	B-33
--------------------------------	------

Service Kits & Accessories

Auxiliary Equipment	H-17
Controllers & Transmitters.....	C-37
Control Valves	D-219
Damper Actuators	E-45
Sensors	B-35
Switches & Relays	G-37
Thermostats	A-75
Variable Frequency Drives	F-25

Service Valves

Application Matrix.....	D-5
Selection Tables	D-55 – D-56
Specifications & Ordering	D-193 – D-205

Signal Converter..... C-15

Signal Selectors, Pneumatic

Highest Pressure.....	G-27
Lowest and Highest.....	G-29
Lowest Pressure	G-31

Single Input Receiver-Controller, Pneumatic..... C-19

Static Pressure and Liquid Level

Regulators, Pneumatic..... C-33

Static Pressure Switch..... G-9

Step Controller, Pneumatic..... C-35

Switches

Accessories & Service Kits	G-37
Differential Static Pressure Airflow	G-11
Enthalpy Control.....	G-7
Positioning.....	G-5
Pressure Electric	G-13
Selector	G-3
Static Pressure.....	G-9
Three-way EP Valves.....	G-15

Subject Index

T

Temperature Controllers, Electronic

Heat Pump	C-7
Refrigeration.....	C-7
Signal Converter	C-15
Time Clock	C-11
Transformer.....	C-13
Universal	C-3

Temperature Transmitters, Pneumatic

Terminal Housing for Magnetic Valves,

ZM, ZM/A.....	D-191
---------------	-------

Thermic Valve Actuator/2-position Control.....

Thermostat Accessories & Service Kits.....

Time Clock for Temperature Controllers.....

Transducers

Electronic-to-Pneumatic.....	G-35
Very Low Differential Pressure.....	B-21

Transformer for Temperature Controllers.....

Transmitters, Pneumatic

Low Differential Pressure.....	C-27
Room and Duct Humidity.....	C-25
Temperature.....	C-23

Tube Fitting Kit, Pneumatic

U

Unit Mounted Pneumatic Thermostats.....

Universal Controllers

VWXY

Valve Actuators, Electric.....	D-71, D-75, D-91, D-93, D-107, D-109, D-111, D-113, D-147, D-149, D-151, D-153, D-159, D-161
--------------------------------	--

Valve Actuators, Pneumatic	D-105, D-141, D-143, D-145
----------------------------------	-------------------------------

Valve Actuators, Thermic.....	D-79
-------------------------------	------

Valve Application Matrix	D-5
--------------------------------	-----

Valve Selection Tables

Ball	D-50 – D-53
Butterfly, 2 to 12-inch	D-57 – D-64
Globe, 1/2 to 2-inch.....	D-23 – D-31
Globe, 2-1/2 to 6-inch.....	D-32 – D-49
High-Pressure Close-off, 2-1/2 to 6-inch.....	D-40 – D-41
Magnetic	D-54
MT/MZ Globe, 1/2 to 1-1/2-inch	D-18 – D-22
Service	D-55 – D-56
Zone	D-16 – D-17

Variable Frequency Drives

Accessories & Service Kits	F-25
SED2 Series.....	F-5
Conventional Bypass	F-9
Electronic (E) Bypass.....	F-15
NEMA Type 3R Bypass.....	F-19

Z

Zone Valves

Application Matrix.....	D-5
Close-off Pressure	D-7
Selection Tables	D-16 – D-17
Specifications & Ordering	D-65 – D-81
Water Capacity.....	D-6

